





ZH	Anschluss-Belegung
	Elektr. Anschluss
	Geometrie Polbild (Steckseite)
..	Ausgangssignal
..	Eingangssignal
..	Datenschnittstelle
..	Teilkreiszusatzspur
37 polig	Kundenseitige Steckerausführung
19; 37	Versorgung 0V (Un); GND
17; 18; 36	Versorgung +V (Up); DC 24 V
Gehäuse	Außenschirm
1	Rechteck-Signal; Din 0
20	Rechteck-Signal; Din 1
2	Rechteck-Signal; Din 2
21	Rechteck-Signal; Din 3
3	Rechteck-Signal; Din 4
22	Rechteck-Signal; Din 5
4	Rechteck-Signal; Din 6
23	Rechteck-Signal; Din 7
5	Rechteck-Signal; Din 8
24	Rechteck-Signal; Din 9
6	Rechteck-Signal; Din 10
25	Rechteck-Signal; Din 11
7	Rechteck-Signal; Din 12
26	Rechteck-Signal; Din 13
8	Rechteck-Signal; Din 14
27	Rechteck-Signal; Din 15
9	Rechteck-Signal; Din 16
28	Rechteck-Signal; Din 17
10	Rechteck-Signal; Din 18
29	Rechteck-Signal; Din 19
11	Rechteck-Signal; Din 20
30	Rechteck-Signal; Din 21
12	Rechteck-Signal; Din 22
31	Rechteck-Signal; Din 23
13	Rechteck-Signal; Dout 0
32	Rechteck-Signal; Dout 1
14	Rechteck-Signal; Dout 2
33	Rechteck-Signal; Dout 3
15	Rechteck-Signal; Dout 4
34	Rechteck-Signal; Dout 5
16	Rechteck-Signal; Dout 6
35	Rechteck-Signal; Dout 7

ZH	Pin configuration
	Electrical connection
	Geometry of pole pattern
..	Output signal
..	Input signal
..	Data interface
..	Additional circular-scale track
37-pin	Customer's connection version
19; 37	Supply 0V (Un); GND
17; 18; 36	Supply +V (Up); DC 24 V
housing	External shield
1	Square-wave signal; Din 0
20	Square-wave signal; Din 1
2	Square-wave signal; Din 2
21	Square-wave signal; Din 3
3	Square-wave signal; Din 4
22	Square-wave signal; Din 5
4	Square-wave signal; Din 6
23	Square-wave signal; Din 7
5	Square-wave signal; Din 8
24	Square-wave signal; Din 9
6	Square-wave signal; Din 10
25	Square-wave signal; Din 11
7	Square-wave signal; Din 12
26	Square-wave signal; Din 13
8	Square-wave signal; Din 14
27	Square-wave signal; Din 15
9	Square-wave signal; Din 16
28	Square-wave signal; Din 17
10	Square-wave signal; Din 18
29	Square-wave signal; Din 19
11	Square-wave signal; Din 20
30	Square-wave signal; Din 21
12	Square-wave signal; Din 22
31	Square-wave signal; Din 23
13	Square-wave signal; Dout 0
32	Square-wave signal; Dout 1
14	Square-wave signal; Dout 2
33	Square-wave signal; Dout 3
15	Square-wave signal; Dout 4
34	Square-wave signal; Dout 5
16	Square-wave signal; Dout 6
35	Square-wave signal; Dout 7

Connection layout ZH 59B37				Pin Layout		Change No: C21656-25	
<small>The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.</small>							
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany				Serie		Version	
				Revision		Sheet	
				D1148816 - 00 - A - 01		Page 1/1	
<small>Document No</small>							