



Toleranztabelle	
L	T
25-150	$\pm 5$
155-450	$\pm 10$
455-900	$\pm 25$
905-1800	$\pm 75$
>1805	$\pm 100$

Biegeradius min. dauernd  
Min. bend radius for flexing

--

Biegeradius min. einmalig  
Min. bend radius for rigid configuration

--

Schleppkettenradius min.  
Min. drag chain radius

--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
For max. cable length (L): See Specifications of the encoder model

886 200 A4

			IDnumber:
			Change No. C029710-78 Phase: Serie
	Original drawing Scale	Format	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Dimensions in mm	1:1	A4	Allgemeintoleranzen ISO 2768-mH $\pm 0,2$ General tolerances ISO 2768-mH $\pm 0,2$

AGK JAE --> Buchsengehäuse 3VB15  
Anschlussmaße

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )

<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany	Document number			1 of 1
	D 1150573 - 00 - A - 02			
	Version	Revision	Sheet	1