



IP	Anschluss-Belegung	
	<b>Elektrischer Anschluss</b>	
	<b>Geometrie Polbild (Steckseite)</b>	
<b>~1Vss</b>	<b>Ausgangssignal</b>	<b>~1Vss</b>
..	<b>Eingangssignal</b>	..
..	<b>Datenschnittstelle</b>	..
..	<b>Teilkreiszusatzspur</b>	..
12 polig	Kundenseitige Steckerausführung	Ader
12	Versorgung 0V (Un)	weißgrün
5	Versorgung 0V (Sensorleitung)	weiß
1	Versorgung +V (Up)	braungrün
11	Versorgung +V (Sensorleitung)	blau
Gehäuse	Außenschirm	Schirm
10	Spannungssignal A+	braun
2	Spannungssignal A-	grün
3	Spannungssignal B+	grau
4	Spannungssignal B-	rosa
7	Spannungssignal R+	rot
8	Spannungssignal R-	schwarz
9	Serielle Schnittstelle serial Data	gelb
6	Serielle Schnittstelle Takt	violett

IP	Pin configuration	
	<b>Electrical connection</b>	
	<b>Geometry of pole pattern (plug side)</b>	
<b>~1Vpp</b>	<b>Output signal</b>	<b>~1Vpp</b>
..	<b>Input signal</b>	..
..	<b>Data interface</b>	..
..	<b>Additional circular scale track</b>	..
12-pin	Customer's connection version	Wire
12	Supply 0V (Un)	white and green
5	Supply 0V (sensor line)	white
1	Supply +V (Up)	brown and green
11	Supply +V (sensor line)	blue
Housing	External shield	Shield
10	Voltage signal A+	brown
2	Voltage signal A-	green
3	Voltage signal B+	grey
4	Voltage signal B-	pink
7	Voltage signal R+	red
8	Voltage signal R-	black
9	Serial interface for serial data	yellow
6	Serial interface for clock	violet

Connection layout IP 4AB12 ~1Vpp .. .. . JH		Pin Layout		Change No: C039509-00	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		<b>D1181773 - 00 - A - 03</b>			Page 1/1
Document No					