



- | | | | | |
|----|----|-----|--------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
| I | II | III | = Montagemöglichkeiten | Mounting options |
| F | | | = Maschinenführung | Machine guideway |
| K | | | = Kundenseitige Anschlussmaße | Required mating dimensions |
| B | | | = Kabelanschluss beidseitig verwendbar | Cable connection usable at either end |
| T | | | = Spannschraube Maßband | Tensioning screw measuring tape |
| D | | | = Druckluftanschluss | Compressed air inlet |
| E | | | = Anschlag | stopper |
| G | | | = Klemmschraube Maßband | clamping screw measuring tape |
| S | | | = Beginn der Messlänge ML
(=100mm absolut) | Beginning of measuring length ML
(=100mm absolute) |
| W | | | = Anlageflächen | Mating surfaces |
| → | | | = Bewegungsrichtung der
Abtasteinheit für Ausgangssignal
gemäß Schnittstellen-Beschreibung | Direction of scanning unit motion for
output signals in accordance with interface
discription |
| ML | | | = Messlänge | Measuring length |

Original drawing		Scale		Format		ID number:	
1:1		A1		A1		C163726-20	
LC 2x1 N einteilig						Series	
LC 2x1 monolithic						Tolerances as per ISO 8015	
Anschlussmaße / Mating Dimensions						General Tolerances ISO 2768-1/2001-mH ±0.2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18015)							
Released		29.04.2026		Version / Revision / Sheet		Page	
DR. JOHANNES HEIDENHAIN GmbH		83301 Traunreut, Germany		D1191439-02 - A-01		1 of 1	