






1f	Anschluss-Belegung	
	Elektrischer Anschluss	
	Geometrie Polbild (Steckseite)	
AMO	Firmenname	AMO
~1Vss	Ausgangssignal	~1Vss
..	Eingangssignal	..
SSI	Datenschnittstelle	SSI
..	Teilkreiszusatzspur	..
17 polig	Kundenseitige Steckerausführung	Ader
10	Versorgung 0V (Un)	weißgrün
7	Versorgung +V (Up)	braungrün
Gehäuse	Außenschirm	Schirm
12	Spannungssignal A+	braun
13	Spannungssignal A-	grün
15	Spannungssignal B+	grau
16	Spannungssignal B-	rosa
14	Serielle Schnittstelle Daten	rot
17	Serielle Schnittstelle Daten invers	schwarz
8	Serielle Schnittstelle Takt	violett
9	Serielle Schnittstelle Takt invers	gelb
1, 2, 3, 4, 5, 6, 11	Freie Adern und Pins	

1f	Pin configuration	
	Electrical connection	
	Geometry of pole pattern (plug side)	
AMO	company name	AMO
~1Vpp	Output signal	~1Vpp
..	Input signal	..
SSI	Data interface	SSI
..	Additional circular scale track	..
17-pin	Customer's connection version	Wire
10	Supply 0V (Un)	white and green
7	Supply +V (Up)	brown and green
Housing	External shield	Shield
12	Voltage signal A+	brown
13	Voltage signal A-	green
15	Voltage signal B+	grey
16	Voltage signal B-	pink
14	Serial interface for data	red
17	Serial interface for data, inverse	black
8	Serial interface for clock	violet
9	Serial interface for clock, inverse	yellow
1, 2, 3, 4, 5, 6, 11	Free wires and pins	

Connection layout 1f 5WS17 ~1Vpp SSI AMO		Pin Layout	Change No: C060730-5
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.			
	Serie	Version	Revision
	D1222133	- 00	- B - 01
	Document No		Page 1/1