



866 200 A3

Biegeradius min. dauernd
Min. bend radius for flexing 45mm

Biegeradius min. einmalig
Min. bend radius for rigid configuration 21mm

Schleppkettenradius min.
Min. drag chain radius 45mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

L +1% bzw. 30mm (or)

max. 42,2

$\phi 6 \pm 0,2$
DIM 6 $\pm 0,2$

ψXX'X

max. 42,7

max. 16

33,3 $\pm 0,13$

			IDnumber:
			Change No. C125296-71 Phase: Serie
	Original drawing Scale	Format	Tolerances as per ISO 8015
	1:1	A3	General Tolerances ISO 2768:1989-mH $\pm 0,2$
Dimensions in mm		AGK JAE (3VB015) --> Sub-D (16S15) Anschlussmaße	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 21.06.2023	Version Revision Sheet D 1231810 - 00 - B - 09 1 of 1
		Document number	