



- I II III = Montagemöglichkeiten / Mounting options
- F = Maschinenführung / Machine guideway
- K = Kundenseitige Anschlussmaße / Required mating dimensions
- B = Kabelanschluss beidseitig verwendbar / Cable connection usable at either end
- C = Spannschraube Maßband / Tensioning screw measuring tape
- D = Druckluftanschluss / Compressed air inlet
- E = Anschlag / stopper
- G = Klemmschraube Maßband / clamping screw measuring tape
- S = Beginn der Messlänge ML (=100mm absolut) / Beginning of measuring length ML (=100mm absolute)
- W = Anlageflächen / Mating surfaces
- = Bewegungsrichtung der Absteinheit für Ausgangssignal gemäß Schnittstellen-Beschreibung / Direction of scanning unit motion for output signals in accordance with interface description
- ML = Messlänge / Measuring length

Original drawing		Scale		Format		ID number:	
1:1		A1				C020580-50	
Dimensions in mm						Change No.	
						C020580-50	
						Phase:	
						Serie	
						Tolerierung nach DIN ISO 8015	
						Tolerances as per DIN ISO 8015	
						Allgemeintol. ISO 2768-mH 36mm:±0.2	
						General tol. ISO 2768-mH 36mm:±0.2	
						(ISO 18015)	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18015)							
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany						Version Revision Sheet Page	
						D1221364-00-A-01	
						1 of 1	