



Toleranztabelle	
L	T
<= 250mm	± 5mm
< 1000mm	+ 10mm

⊗	Signaladern	
⊗	Biegeradius min. einmalig / min. bend radius for rigid configuration	5mm
⊗	Aderdurchmesser	0,81mm
⊗	Querschnitt / Cross section	0,15mm <sup>2</sup> / AWG26
⊗	Durchmesser / Diameter	1,8mm
⊗	Arbeitsspannung	50V
⊗	Prüfspannung	3,4kV
⊗	Temperaturbereich	-65°C / +150°C

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
 For max. cable length (L): See Specifications of the encoder model

			IDnumber:
			Change No. C165519-10 Phase: Serie
	Original drawing Scale	Format	AGK E30 90B012 --> 01
Dimensions in mm	1:1	A3	Anschlussmaße
			Tolerances as per ISO 8015
			General Tolerances ISO 2768:1989-mH ±0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 07.12.2023	Version   Revision   Sheet D 1277276-02-B -06 1 of 1
		Document number	