




D	±T
>Ø50.00 - ≤ Ø60.00	0.005
>Ø60.00 - ≤ Ø70.00	0.006
>Ø70.00 - ≤ Ø80.00	0.008
>Ø80.00 - ≤ Ø120.00	0.010
>Ø120.00 - ≤ Ø180.00	0.015
>Ø180.00 - ≤ Ø250.00	0.020
>Ø250.00 - ≤ Ø370.00	0.030
>Ø370.00 - ≤ Ø500.00	0.045
>Ø500.00 - ≤ Ø660.00	0.060
>Ø660.00	0.080


LPR = 78.5398 x D + 33.1942 round down result to integer /
Ergebnis auf ganze Zahl abrunden
DA = D - 0.5

LPR =lines per revolution / Strichzahl pro Umdrehung
M = rotary axis / Rotationsachse
D = scanning diameter / Abtastdurchmesser
DA = mating diameter / Aufnahmedurchmesser
T = tolerance mating diameter / Toleranz Aufnahmedurchmesser

S = optical centerline / optische Mittellinie
C = cable / Anschlusskabel
K = customer mounting dimensions / kundenseitige Anschlussmaße
R = bending radius / Biegeradius: stat. R ≥ 8mm, dyn. R ≥ 20mm
L = LED function display / LED Funktionsanzeige
RI = reference mark(s) / Referenzmarke(n)

Permissible position deviation scanning head - tape scale ring A B
Zulässige Lageabweichungen Abtasteinheit - Maßbandring A B

$\varphi_Z = \pm 1.00\text{mrad}$ or / oder $\pm 0.06^\circ$ (yaw angle / Gierwinkel)
 $\varphi_Y = \pm 1.50\text{mrad}$ or / oder $\pm 0.09^\circ$ (pitch angle / Nickwinkel)
 $\varphi_X = \pm 4.00\text{mrad}$ or / oder $\pm 0.23^\circ$ (roll angle / Rollwinkel)
 $\Delta_Z = \pm 0.15$ Gap tolerance / Abstandstoleranz
 $\Delta_Y = \pm 0.5$ Displacement / Verschiebung

			ID number:					
			Change No.	C139591-91				
			Phase:	Serie				
	Original drawing		MSR15 MBR MSR15 MBR Anschlussmaße / Mating Dimensions					
	Scale	Format						
Dimensions in mm	2:1	A3	Tolerances as per ISO 8015					
			General Tolerances ISO 2768:1989-mH ≤ 6:±0.2					
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)								
 www.rsfsf.at			Released	Version	Revision	Sheet	Page	
			18.10.2024	D1305425-03-A-01				1 of 1
				Document number				