


Stecker	Typ	ID-Nr.
Sub-D (Z13)	Specto 30X8A	1336827
Sub-D (Z13)	Specto 30X8A	1370079
Sub-D (Z13)	Metro 30X8A	1371619
Sub-D (Z13)	Metro 30X8A	1371620
Rundstecker M23 (Z14)	Specto 30X8A	1453695
Rundstecker M23 (Z14)	Metro 30X8A	1453721



1413962 A3

01A Variante Z13

01A Variante Z14

Ansicht auf Messspitze Ansicht auf Kabelausgang
(ohne Stecker)

- (H1) =Klemmbereich / clamping area
- (R) =Referenzmarken-Lage / referencemark position
- (S) =Beginn der Messslänge ML / beginning of measuring length ML

Original drawing		ST/MT 30X8 A		Change No.	C179777-05
Scale		MI1218 radial		Phase:	Serie
Format		Anschlussmaße / Mating Dimensions		Tolerances as per ISO 8015	
Dimensions in mm	1:1	A3	General Tolerances ISO 2768:1989-mK ≤ 6mm:±0,2		
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
NUMERIK JENA GmbH Im Semmicht 4 07751 Jena			Released	Version	Revision
			28.05.2025		
			1336827-01 - A-01		Sheet
			Document number		Page
					1 of 1