



- 1 = Tightening torque of the M4 - 8.8 cylinder head screw: $2,5 \text{ Nm} \pm 0,13 \text{ Nm}$
- 2 = Mark of 0° position $\pm 5^\circ$
- 3 = Direction of rotation for ascending position values
- 4 = LED position
- 5 = Permitted for shaft clamping
- 6 = Blocking area for flex PCB

		ID number:	
		Change No. C112975-15	Series
		Phase:	
		Tolerances as per ISO 8015	
		General Tolerances ISO 2768:1989-mH $\leq 6\text{mm}:\pm 0,2$	
	Original drawing	MRS 2280 MRS 2280 Anschlussmaße / Mating Dimensions	
Scale	Format		
Dimensions in mm	3:2 A3		
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released	Version Revision Sheet Page
		05.05.2021	D1254464-00-L-01 Document number