



- |  |  |
|--|--|
| <b>A</b> = Lagerung Kundenwelle  | Bearing for customer shaft                                 |
| <b>H1</b> = Teilungseite TK  | Scale surface TK   |
| <b>H2</b> = Montageseite TK  | Mounting surface TK  |
| <b>H3</b> = Auf der Feinspur (Ø 48.0 mm bis Ø 57.0 mm), nach der Montage | On the fine track (Ø 48.0 mm to Ø 57.0 mm), after mounting |
| <b>H4</b> = Zentrierkreis TK   | Centering circle TK  |
| $\sqrt[0.2]{A}$ nach der Montage   | $\sqrt[0.2]{A}$ after mounting                             |

		ID number:	
		Change No.	C115808-12
		Phase:	Serie
	Original drawing	<b>KCI 120 Dplus - TK Messgerät A</b> <b>KCI 120 Dplus - TK Encoder A</b> Anschlussmaße / Mating Dimensions	
	Scale   Format		
Dimensions in mm	2:1   A3	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015	
		Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version	Revision
		Sheet	Page
		<b>D1356823-00-A-01</b>	
		Document number	
		1 of 1	