


Kabel mit Schutzschlauch  
cable with Armor



- M = Maschinenführung / machine guideway
- ML = Messlänge / measuring length
- ↔ = 0 ... ML
- C = Anschlusskabel / cable
- CL = Kabellänge / cable length
- P = Luftanschluss / air inlet
- (K) = kundenseitige Anbaumaße / required mating dimensions
- (S) = Beginn der Messlänge ML / beginning of measuring length ML

		ID number:		
		Change No.	C096131-72	
		Phase:	Serie	
		Tolerances as per ISO 8015		
		General Tolerances ISO 2768:1989-mH	≤ 6±0.2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of a patent, utility model or design. (ISO 16016)				
		Released	Version	Revision
		30.04.2021		
		D1340474-00 - B-01		Page
		Document number		1 of 1

**RSF Elektronik**  
www.rsf.at