


- H1** Sensorfläche
Sensor surface
- H2** Zu prüfendes Werkzeug
Tool to be tested
- H3** Kabelanschluss: 8-Polig M12
Cable connection: 8-pin M12
- H4** Zwei M5 Zylinderschrauben, Anzugsmoment: 6.0 Nm
Two M5 cylinder head screws, tightening torque: 6.0 Nm
- H5** Zustandsanzeige LED
Status display LED
- H6** Messweg
Measuring path

886 200 A4

			ID number: 1377561
			Change No. C167557-18 Phase: Serie
	Original drawing		TD 110 TD 110 Anschlussmaße / Mating Dimensions
	Scale	Format	
Dimensions in mm	1:1	A4	General Tolerances ISO 2768:1989-mH $\leq 6\text{mm} \pm 0,2$
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released	Version Revision Sheet Page
		06.10.2025	D1385957-01-A-01 1 of 1
		Document number	