



- A** = Lagerung Kundenwelle Bearing for customer shaft
- H1** = Teilungseite TK Scale surface TK
- H2** = Montageseite TK Mounting surface TK
- H3** = Auf der Feinspur (Ø 31.0 mm bis Ø 38.5 mm), nach der Montage On the fine track (Ø 31.0 mm to Ø 38.5 mm), after mounting
- H4** = Zentrierkreis TK Centering circle TK

↗ 0.3 A
nach der Montage

↗ 0.3 A
after mounting

| | | | | |
|---|------------------|--------|---|------------|
| | | | ID number: | |
| | | | Change No. | C115808-11 |
| | | | Phase: | Serie |
| | Original drawing | | KCI 120 Dplus - TK Messgerät B KCI 120 Dplus - TK Encoder B Anschlussmaße / Mating Dimensions | |
| | Scale | Format | | |
| Dimensions in mm | 2:1 | A3 | Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2 | |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | | Version | Revision |
| | | | Sheet | Page |
| | | | D1356812-00-A-01 Document number | |
| | | | 1 of 1 | |