


..	Anschluss-Belegung	
	Elektrischer Anschluss	
..	Geometrie Polbild (Steckseite)	
JH	Firmenname	JH
..	Ausgangssignal	..
..	Eingangssignal	..
EnDat22	Datenschnittstelle	EnDat22
..	Teilkreiszusatzspur	..
10 polig	Kundenseitige Steckerausführung	10 polig
7	Versorgung 0V (Un)	weißgrün
3	Versorgung 0V (Sensorleitung)	weiß
5	Versorgung +V (Up)	braungrün
1	Versorgung +V (Sensorleitung)	blau
Im Messgerät	Versorgung verbunden mit Sensorleitung	Im Messgerät
Flachsteckerhülse	Außenschirm	Schirm
2	Serielle Datenübertragung Daten	grau
4	Serielle Datenübertragung Daten invers	rosa
6	Serielle Datenübertragung Takt	violett
8	Serielle Datenübertragung Takt invers	gelb
9	Freie Adern und Pins	
10	Freie Adern und Pins	

..	Pin configuration	
	Electrical connection	
..	Geometry of pole pattern (plug side)	
JH	company name	JH
..	Output signal	..
..	Input signal	..
EnDat22	Data interface	EnDat22
..	Additional circular scale track	..
10-pin	Customer's connection version	10-pin
7	Supply 0V (Un)	white and green
3	Supply 0V (sensor line)	white
5	Supply +V (Up)	brown and green
1	Supply +V (sensor line)	blue
In the encoder	Supply connected with sensor line	In the encoder
Flat connector sleeve	External shield	Shield
2	Serial data transfer of data	grey
4	Serial data transfer of data, inverted	pink
6	Serial data transfer of clock pulse	violet
8	Serial data transfer of clock pulse, inverted	yellow
9	Free wires and pins	
10	Free wires and pins	