





Jc	Anschluss-Belegung	
	Elektrischer Anschluss	
	Geometrie Polbild (Steckseite)	
JH	Firmenname	JH
~1Vss	Ausgangssignal	~1Vss
..	Eingangssignal	..
..	Datenschnittstelle	..
..	Teilkreiszusatzspur	..
9 polig	Kundenseitige Steckerausführung	Ader
8	Versorgung 0V (Un)	weißgrün
9	Versorgung +V (Up)	braungrün
Gehäuse	Außenschirm	Schirm
5	Spannungssignal A+	braun
4	Spannungssignal A-	grün
1	Spannungssignal B+	grau
2	Spannungssignal B-	rosa
7	Spannungssignal R+	rot
6	Spannungssignal R-	schwarz
3	Freie Adern und Pins	
	Freie Adern und Pins	blau, weiß, gelb, violett

Jc	Pin configuration	
	Electrical connection	
	Geometry of pole pattern (plug side)	
JH	company name	JH
~1Vpp	Output signal	~1Vpp
..	Input signal	..
..	Data interface	..
..	Additional circular scale track	..
9-pin	Customer's connection version	Wire
8	Supply 0V (Un)	white and green
9	Supply +V (Up)	brown and green
Housing	External shield	Shield
5	Voltage signal A+	brown
4	Voltage signal A-	green
1	Voltage signal B+	grey
2	Voltage signal B-	pink
7	Voltage signal R+	red
6	Voltage signal R-	black
3	Free wires and pins	
	Free wires and pins	blue, white, yellow, violet

Connection layout Jc 16S09 ~1Vpp JH		Pin Layout		Change No. C149918-10	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		D1403665 - 00 - A - 01			Page 1/1
Document No					