



70	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
~1Vss	Ausgangssignal
..	Eingangssignal
..	Datenschnittstelle
Z1	Teilkreiszusatzspur
14 polig	Kundenseitige Steckerausführung
5b	Versorgung 0V (Un)
3a	Versorgung 0V (Sensorleitung)
1b	Versorgung +V (Up)
7a	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
Flansch, Kappe	Außenschirm
6b	Spannungssignal A+
2a	Spannungssignal A-
3b	Spannungssignal B+
5a	Spannungssignal B-
4b	Spannungssignal R+
4a	Spannungssignal R-
7b	Kommutierungssignal C+(Z1-Spur)
1a	Kommutierungssignal C-(Z1-Spur)
2b	Kommutierungssignal D+(Z1-Spur)
6a	Kommutierungssignal D-(Z1-Spur)

70	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
~1Vpp	Output signal
..	Input signal
..	Data interface
Z1	Additional circular scale track
14-pin	Customer's connection version
5b	Supply 0V (Un)
3a	Supply 0V (sensor line)
1b	Supply +V (Up)
7a	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
Flange, housing	External shield
6b	Voltage signal A+
2a	Voltage signal A-
3b	Voltage signal B+
5a	Voltage signal B-
4b	Voltage signal R+
4a	Voltage signal R-
7b	Commutation signal C+(Z1 track)
1a	Commutation signal C-(Z1 track)
2b	Commutation signal D+(Z1 track)
6a	Commutation signal D-(Z1 track)

Connection layout 70 62S14 ~1Vpp Z1 JH				Pin Layout		Change No: C152702-3	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D319274 - 00 - B - 02				1/1	
83301 Traunreut, Germany		Document No					