





<b>04</b>	<b>Anschluss-Belegung</b>	
	<b>Elektrischer Anschluss</b>	
	<b>Geometrie Polbild (Steckseite)</b>	
<b>JH</b>	<b>Firmenname</b>	<b>JH</b>
~11µAss	<b>Ausgangssignal</b>	~11µAss
..	<b>Eingangssignal</b>	..
..	<b>Datenschnittstelle</b>	..
..	<b>Teilkreiszusatzspur</b>	..
9 polig	Kundenseitige Steckerausführung	Ader
4	Versorgung 0V (Un)	weiß
3	Versorgung +V (Up)	braun
Gehäuse	Außenschirm	Schirm
9	Innenschirm (0V)	weißbraun/SS
1	Stromsignal (4x90°) 0° +	grün
2	Stromsignal (4x90°) 0° -	gelb
5	Stromsignal (4x90°) 90° +	blau
6	Stromsignal (4x90°) 90° -	rot
7	Stromsignal (4x90°) RI +	grau
8	Stromsignal (4x90°) RI -	rosa
	Freie Adern und Pins	braungrün
0035	Ergänzungen	0035

0035 = Ader braungrün nur bei Kabeldurchmesser 4,5mm vorhanden

<b>04</b>	<b>Pin configuration</b>	
	<b>Electrical connection</b>	
	<b>Geometry of pole pattern (plug side)</b>	
<b>JH</b>	<b>company name</b>	<b>JH</b>
~11µApp	<b>Output signal</b>	~11µApp
..	<b>Input signal</b>	..
..	<b>Data interface</b>	..
..	<b>Additional circular scale track</b>	..
9-pin	Customer's connection version	Wire
4	Supply 0V (Un)	white
3	Supply +V (Up)	brown
Housing	External shield	Shield
9	Internal shield (0 V)	white and brown/SS
1	Current signal (4x90°) 0° +	green
2	Current signal (4x90°) 0° -	yellow
5	Current signal (4x90°) 90° +	blue
6	Current signal (4x90°) 90° -	red
7	Current signal (4x90°) RI +	grey
8	Current signal (4x90°) RI -	pink
	Free wires and pins	brown and green
0035	Additions	0035

0035 = Wire brown and green only available for cable diameter 4.5mm

Connection layout 04 38S09 ~11µApp .. .. JH		Pin Layout		Change No. C027508-5	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		<b>D295051</b>	<b>- 00</b>	<b>- B</b>	<b>- 13</b>
		Document No			Page 1/1