





30	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
~1Vss	Ausgangssignal
..	Eingangssignal
..	Datenschnittstelle
..	Teilkreiszusatzspur
12 polig	Kundenseitige Steckerausführung
1a	Versorgung 0V (Un)
1b	Versorgung 0V (Sensorleitung)
2a	Versorgung +V (Up)
2b	Versorgung +V (Sensorleitung)
Flansch, Kappe	Außenschirm
6b	Spannungssignal A+
6a	Spannungssignal A-
5b	Spannungssignal B+
5a	Spannungssignal B-
4b	Spannungssignal R+
4a	Spannungssignal R-
3a	Freie Adern und Pins
3b	Freie Adern und Pins

30	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
~1Vpp	Output signal
..	Input signal
..	Data interface
..	Additional circular scale track
12-pin	Customer's connection version
1a	Supply 0V (Un)
1b	Supply 0V (sensor line)
2a	Supply +V (Up)
2b	Supply +V (sensor line)
Flange, housing	External shield
6b	Voltage signal A+
6a	Voltage signal A-
5b	Voltage signal B+
5a	Voltage signal B-
4b	Voltage signal R+
4a	Voltage signal R-
3a	Free wires and pins
3b	Free wires and pins

connection layout 30 62S12 ~1Vss				Pin Layout		Change No: C152702-20	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D297243	- 00	- A	- 03	1/1	
83301 Traunreut, Germany		Document No					