




- A** = Lagerung Kundenwelle
- K** = Kundenseitige Anschlussmaße
- M** = Messpunkt Arbeitstemperatur
- H1** = Klemmschraube für Kupplungsring - SW 2
Anzugsmoment 1,25 -0,2 Nm
- H2** = ERN Stiftleiste 12-pol.
ERN mit Z1-Spur Stiftleiste 14-pol.
ERN mit Block-Kommutierung Stiftleiste 16-pol.
ECN/EQN Stiftleiste 12-pol.
ECN/EQN Stiftleiste 12-pol. +4-pol.
- H3** = Gussdeckel
- H4** = Selbstsichernde Schraube M5 x 50 DIN 6912 - SW 4
Anzugsmoment 5 +0,5 Nm
- H5** = ERN Referenzmarkenlage Welle - Kappe
ECN/EQN Nullposition Welle - Kappe
- H6** = Verschlusschraube SW3 und 4
Anzugsmoment 5 +0,5 Nm
- H7** = Befestigung für Kabel mit Crimp-Hülse ϕ 6 +0,3 x 10
- H8** = Abdrückgewinde M10
- H9** = Abdrückgewinde M6
- H10** = Ausgleich von Montagetoleranzen und thermischer Ausdehnung, keine dynamische Bewegung

- Bearings for customer shaft
- Required mating dimensions
- Operating temperature measuring point
- Locking screw for coupling ring - SW 2
torque 1,25 -0,2 Nm
- ERN 12-pin connector
ERN with Z1-track 14-pin connector
ERN with block-commutating 16-pin connector
ECN/EQN 12-pin connector
ECN/EQN 12-pin + 4-pin connector
- Die-cast cover
- Self-locking screw M5 x 50 DIN 6912 - SW4
torque 5 +0,5 Nm
- ERN reference mark position shaft - housing
ECN/EQN Datum position shaft - housing
- Locking screw SW3 and 4
torque 5 +0,5 Nm
- Mounting for cable with crimp barrel of ϕ 6 +0,3 x 10
- Back-off thread M10
- Back-off thread M6
- Compensation of mounting tolerances and thermal expansion, no dynamic motion

65B	06	37A/37D
WELLA1	KUPPA1	FOKAA1

					ID number:			
					Change No. C151346-5			
					Phase: Serie			
	Original drawing		ERN/ECN/EQN 13xx ERN/ECN/EQN 13xx Anschlussmaße / Mating Dimensions					
	Scale	Format						
Dimensions in mm	1:1	A2	Tolerances as per ISO 8015 General Tolerances ISO 2768:1989-mH ±6mm:±0,2					
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)								
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Released		Version	Revision	Sheet	Page
			30.10.2023		D 374033-08-B-01			1 of 1
			Document number					