






- A = Lagerung Kundenwelle
- K = Kundenseitige Anschlussmaße
- M1 = Messpunkt Arbeitstemperatur
- M2 = Messpunkt Vibration
- H1 = Klemmschraube für Kupplungsring - SW 2
Anzugsmoment: 1,25 - 0,2 Nm
- H2 = Selbstsichernde Schraube M5 x 50 DIN 6912 - SW 4
Anzugsmoment: 5 + 0,5 Nm
- H3 = Verschlusschraube SW 3 und 4
Anzugsmoment: 5 + 0,5 Nm
- H4 = Abdrückgewinde M10
- H5 = Abdrückgewinde M6
- H6 = Ausführung Geber mit Flanschdose
- H7 = Ausgleich von Montagetoleranzen und thermischer Ausdehnung, keine dynamische Bewegung
- H8 = Drehrichtung der Welle für Ausgangssignale gemäß Schnittstellenbeschreibung

Bearing of mating shaft

Required mating dimensions

Measuring point for operating temperature

Measuring point for vibration

Locking screw for coupling ring - AF 2
Tightening torque: 1.25 -0.2 Nm

Self-locking screw M5 x 50 DIN 6912 - AF 4
Tightening torque: 5 +0.5 Nm

Locking screw AF 3 and 4
Tightening torque: 5 +0.5 Nm

Back-off thread M10


Back-off thread M6

Encoder version with flange socket

Compensation of mounting tolerances and thermal expansion, no dynamic motion

Direction of shaft rotation according to interface description

65B	06
WELLA1	KUPPA1

				ID number:						
				Change No. C172391-15						
				Phase: Serie						
		Original drawing		ERN/ECN/EQN 4xx ERN/ECN/EQN 4xx Anschlussmaße / Mating Dimensions		Tolerances as per ISO 8015				
		Scale	Format			General Tolerances ISO 2768:1989-mH ±6mm±0,2				
Dimensions in mm		1:1	A2							
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)										
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany				Released		Version	Revision	Sheet	Page	
				06.10.2025		D 376961-08-A-01			1	1
				Document number						