


ANELA2 16S015-VB



ANELA1 0ZB015-F9

≥.4"	≥10	≥2"	≥50	* 1,64	* 0,5	∅4,5 DIA .18"
inch	mm	inch	mm	ft	m	
Einmalige Biegung Rigid configuration		Dauerbiegung Frequent flexing		Standard		
Biegeradius R min. Bending radius R min.				Kabellänge L Cable length L		

larger cable lengths are available as per specifications

\* = größere Kabellängen entsprechend Geräte-Spezifikation

Cable length L = Kabellänge

Male = Stift

Female = Buchse

			IDnumber:
			Release number: R6743
	Original drawing	EIB 3391Y	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Dimensions in mm	Scale: 1:1	Format: A3	Allgemeintoleranzen ISO 2768-mH <6mm: ± 0.2 General tolerances ISO 2768-mH <6mm: ± 0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version   Revision   Sheet D 383021 - 00 - A - 02 1 of 1
			Document number