



- | | |
|---|--|
| A = Lagerung Kundenwelle | Bearings for customer shaft |
| K = Kundenseitige Anschlussmasse | Required mating dimensions |
| M = Meßpunkt Arbeitstemperatur | Operating temperature measuring point |
| H1 = Selbstsichernde Schraube M5 x 50
DIN 6912 - SW 4
Anzugsmoment 5 +0.5 Nm | Self-locking-screw M5 x 50
DIN 6912 - SW4
torque 5 +0,5 Nm |
| H2 = Verschlusschraube SW 3 und 4
Anzugsmoment 5 +0.5 Nm | Locking screw SW 3 and 4
Anzugsmoment 5 +0,5 Nm |
| H3 = Abdrückgewinde M10 | back-off thread M10 |
| H4 = Abdrückgewinde M6 | back-off thread M6 |
| H5 = Ausgleich von Montagetoleranzen
und thermischer Ausdehnung,
keine dynamische Bewegung | Compensation of mounting
tolerances and thermal expansion,
no dynamic motion |

65B 14
WELLA1 KUPPA1

Original drawing		ERN 4xx		ID number:
Scale	Format	ERN 4xx		Change No. C151346-05
Dimensions in mm	1:1 A2	Anschlussmaße / Mating Dimensions		Phase: Serie
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)				Tolerances as per ISO 8015
General Tolerances ISO 2768:1989-mH ± 6mm: ± 0.2				
Released		Version	Revision	Sheet
30.10.2023				Page
HEIDENHAIN		D 509630-05-A-01		1 of 1
DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Document number		