



- A** = Lagerung Kundenwelle
- B** = Lagerung Geber
- K** = Kundenseitige Anschlussmaße
- M1** = Messpunkt Arbeitstemperatur
- M2** = Messpunkt Vibration
- H1** = ERN 1331 Stiftleiste 12-pol.
ERN 1381 Stiftleiste 14-pol.
ERN 1387 Stiftleiste 14-pol.
EQN 1325 Stiftleiste 12-pol.
EQN 1337 Stiftleiste 12pol.+4pol.
ECN 1325 Stiftleiste 12pol.+4pol.
- H2** = Befestigung für Kabel mit Crimp-Hülse $\phi 6 +0,3 \times 10$
- H3** = Gussdeckel
- H4** = Verschlusschraube SW 3 und 4
Anzugsmoment: 5 -1 Nm
- H5** = ERN Referenzmarkenlage Welle - Kappe
ECN/EQN Nullposition Welle - Kappe
- H6** = Abdrückgewinde nach entfernter Befestigungsschraube
- H7** = Abdrückgewinde für gelöste Befestigungsschraube
- H8** = ERN: Drehrichtung der Welle für Ausgangssignale
gemäß Schnittstellenbeschreibung
ECN/EQN: Drehrichtung der Welle für steigende Positionswerte

- Bearing of mating shaft
- Bearing of encoder
- Required mating dimensions
- Measuring point for operating temperature
- Measuring point for vibration
- ERN 1331 12-pin connector
ERN 1381 14-pin connector
ERN 1387 14-pin connector
EQN 1325 12-pin connector
EQN 1337 12-pin + 4-pin connector
ECN 1325 12-pin + 4-pin connector
- Mounting for cable with crimp barrel of $\phi 6 +0.3 \times 10$
- Die-cast cover
- Locking screw AF 3 and 4
Tightening torque: 5 -1 Nm
- ERN reference mark position shaft - housing
ECN/EQN Datum position shaft - housing
- Back-off thread after mounting screw has been removed
- Back-off thread for loosened mounting screw
- ERN: Direction of shaft rotation for output signals
as per the interface description
ECN/EQN: Direction of shaft rotation for ascending
position values

65B	37B	ID number:	
WELLA1	FOKAA1	Change No. C172391-15	
		Phase: Serie	
		Tolerances as per ISO 8015	
		General Tolerances ISO 2768:1989-mH $\pm 0,2$	
		The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)	
		Released	Version Revision Sheet Page
DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		06.10.2025	D 528719-13-C-01 1 of 1