




- A** = Lagerung Kundenwelle
- K** = Kundenseitige Anschlußmaße
- M** = Meßpunkt Arbeitstemperatur
- H2** = ERN Stiftleiste 14-pol.
ECN/EQN Stiftleiste 12-pol.
ECN/EQN Stiftleiste 12-pol. + 4-pol.
- H3** = Gußdeckel
- H4** = ERN Referenzmarkenlage Welle - Kappe
- H5** = Selbstsichernde Schraube M5 x 50 DIN 6912 - SW 4
Anzugsmoment 5+0,5 Nm
- H6** = Verschlussschraube SW3 und 4
Anzugsmoment 5+0,5 Nm
- H7** = Befestigung für Kabel mit Crimp-Hülse ϕ 6+0,3 x 10
- H8** = Abdrückgewinde M10
- H9** = Abdrückgewinde M6
- H10** = Ausgleich von Montagetoleranzen und thermischer Ausdehnung, keine dynamische Bewegung

- Bearings for customer shaft
- Required mating dimensions
- Operating temperature measuring point
- ERN 14-pin connector
ECN/EQN 12-pin connector
ECN/EQN 12-pin + 4-pin connector
- Die-cast cover
- ERN referenc marl position shaft - housing
- Self-locking screw M5 x 50 DIN 6912 - SW4
torque 5+0,5 Nm
- Locking screw SW3 and 4
torque 5+0,5 Nm
- mounting for cable with crimp barrel of ϕ 6+0,3 x 10
- back-off thread M10
- back-off thread M6
- Compensation of mounting tolerances and thermal expansion, no dynamic motion

65B	12	WELLA1 KUPPA1
		ID number:
		Change No. C151346-05
		Phase: Serie
		Tolerances as per ISO 8015
		General Tolerances ISO 2768:1989-mH $\approx$ 6mm: $\pm$ 0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)		
		Released
		Version
		Revision
		Sheet
		Page
		1 of 1
		Document number
		D 530577-04 - A-01