



- A** = Lagerung Kundenwelle Bearings for customer shaft
- K** = Kundenseitige Anschlußmaße Required mating dimensions
- M** = Messpunkt Arbeitstemperatur Operating temperature measuring point
- H1** = Selbstsichernde Schraube M5 x 50 Self-locking-screw M5 x 50
DIN 6912 - SW 4 torque 5 +0,5 Nm
- H2** = Verschlussschraube SW 3 und 4 locking screw SW 3 and 4
Anzugsmoment 5 +0.5 Nm torque 5 +0.5 Nm
- H3** = Abdrückgewinde M10 back-off thread M10
- H4** = Abdrückgewinde M6 back-off thread M6
- H5** = Ausgleich von Montagetoleranzen Compensation of mounting
und thermischer Ausdehnung, tolerances and thermal expansion,
keine dynamische Bewegung no dynamic motion

65B	47A
WELLA1	KUPPA1

Original drawing		ERN 4xx		ID number:
Scale	Format	ERN 431		Change No. C151346-05
Dimensions in mm	1:1	Anschlussmaße / Mating Dimensions		Phase: Serie
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of a patent, utility model or design. (ISO 16016)				Tolerances as per ISO 8015
General Tolerances ISO 2768:1989-mH ±0.2				
Released		Version	Revision	Sheet
30.10.2023				Page
DR. JOHANNES HEIDENHAIN GmbH		D 517600-03-A-01		1 of 1
83301 Traunreut, Germany		Document number		