





R8	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
~1Vss	Ausgangssignal
..	Eingangssignal
EnDat01	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
14	Versorgung 0V (Un)
12	Versorgung 0V (Sensorleitung)
13	Versorgung +V (Up)
11	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
1	Spannungssignal A+
2	Spannungssignal A-
3	Spannungssignal B+
4	Spannungssignal B-
7	Serielle Datenübertragung Daten
8	Serielle Datenübertragung Daten invers
9	Serielle Datenübertragung Takt
10	Serielle Datenübertragung Takt invers
5	Freie Adern und Pins
6	Freie Adern und Pins
15	Freie Adern und Pins

R8	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
~1Vpp	Output signal
..	Input signal
EnDat01	Data interface
..	Additional circular scale track
15-pin	Customer's connection version
14	Supply 0V (Un)
12	Supply 0V (sensor line)
13	Supply +V (Up)
11	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
1	Voltage signal A+
2	Voltage signal A-
3	Voltage signal B+
4	Voltage signal B-
7	Serial data transfer of data
8	Serial data transfer of data, inverted
9	Serial data transfer of clock pulse
10	Serial data transfer of clock pulse, inverted
5	Free wires and pins
6	Free wires and pins
15	Free wires and pins

Connection layout R8 5PS15 ~1Vpp EnDat01				Pin Layout		Change No: 97414	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D533387	- 01	- B	- 01	1/1	
83301 Traunreut, Germany		Document No					