



C4	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
..	Ausgangssignal
..	Eingangssignal
EnDat22	Datenschnittstelle
..	Teilkreiszusatzspur
8 polig	Kundenseitige Steckerausführung
5	Versorgung 0V (Un)
1	Versorgung 0V (Sensorleitung)
8	Versorgung +V (Up)
2	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
Gehäuse	Außenschirm
3	Serielle Datenübertragung Daten
4	Serielle Datenübertragung Daten invers
7	Serielle Datenübertragung Takt
6	Serielle Datenübertragung Takt invers

C4	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
..	Output signal
..	Input signal
EnDat22	Data interface
..	Additional circular scale track
8-pin	Customer's connection version
5	Supply 0V (Un)
1	Supply 0V (sensor line)
8	Supply +V (Up)
2	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
Housing	External shield
3	Serial data transfer of data
4	Serial data transfer of data, inverted
7	Serial data transfer of clock pulse
6	Serial data transfer of clock pulse, inverted

Connection layout C4 5XB08 .. EnDat22 JH				Pin Layout		Change No. C152702-3	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D532351	- 00	- C	- 18	1/1	
83301 Traunreut, Germany		Document No					