







$U_p = 5V \pm 5\%$
(I max. 130 mA)

EN 50 178/4.98; 5.2.9.5
IEC 364-4-41: 1992; 411 (PELV/SELV)
(siehe, see HEIDENHAIN D231 929)



DIN EN 100 015 - 1
CECC 00015 - 1





HEIDENHAIN

Montageanleitung
Mounting Instructions

ERN 1381.020


3/2006

62S14-70



Schirm auf Gehäuse
Shield on housing

6b	2a	3b	5a	4b	4a	7a	3a	1b	5b
A		B		R		Sensor U_p	Sensor 0V	U_p	0V
+	-	+	-	+	-				



DR. JOHANNES HEIDENHAIN GmbH

Dr.-Johannes-Heidenhain-Straße 5

83301 Traunreut, Germany

☎ +49 (86 69) 31-0

FAX +49 (86 69) 50 61

e-mail: info@heidenhain.de

Technical support FAX +49 (86 69) 31-10 00

Measuring systems ☎ +49 (86 69) 31-31 04

e-mail: service.ms-support@heidenhain.de

TNC support ☎ +49 (86 69) 31-31 01

e-mail: service.nc-support@heidenhain.de

NC programming ☎ +49 (86 69) 31-31 03

e-mail: service.nc-pgm@heidenhain.de

PLC programming ☎ +49 (86 69) 31-31 02

e-mail: service.plc@heidenhain.de

Lathe controls ☎ +49 (7 11) 95 28 03-0

e-mail: service.hsf@heidenhain.de

www.heidenhain.de



Ve 00

546 270-91 · 20 · 3/2006 · H · Printed in Germany

Änderungen vorbehalten · Subject to change without notice



