




I II III = Montagemöglichkeiten

F = Maschinenführung

P = Messpunkte zum Ausrichten

K = Kundenseitiges Anschlussmaß

A = Alternatives kundenseitiges Anschlussmaß

B = Kabelanschluss

D = Druckluftanschluss

T = Mechanischer Fixpunkt, bevorzugt verwenden

H = Mechanischer Fixpunkt kompatibel zu Vorgängergeräte

G = Mechanischer Fixpunkt im 100mm Raster

W = Anlagefläche

S = Beginn der Messlänge ML (=20mm absolut)

➡ = Bewegungsrichtung der Absteinheit für Ausgangssignale gemäß Schnittstellen - Beschreibung

ML = Messlänge

Mounting options

Machine guideway

Gauging points for alignment

Required mating dimensions

Alternative mating dimensions

Cable connection usable at either end

Compressed air inlet usable at either end

Mechanical fixed point (to be preferred)


Mechanical fixed point, compatible to predecessor model

Mechanical fixed point (coincides with the spacing interval of 100mm)
Mating surfaces

Beginning of measuring length ML (=20mm absolute)

Direction of scanning unit motion for output signals in accordance with interface description

Measuring length

ML		P		Punkte gleichmäßig entlang des Profils verteilt Points uniformly distributet along the profile
IA	840	P1,P2		
IA	1740	P1,P2,P3		
IA	3040	P1,P2,P3,P4		
IA	4240	P1,P2,P3,P4,P5		
				ID number:
Change No.				R7024
Phase:				Serie
				Tolerances as per ISO 8015
				General Tolerances ISO 2768:1999-mH ± 6mm; ± 0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18016)				
		Original drawing	LC 183/193F/193M	
Dimensions in mm		Scale	LC 183/193F/193M	
		Format	Anschlussmaße / Mating Dimensions	
1:1		A1		

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18016)

HEIDENHAIN		Released	Version Revision Sheet	Page
DR. JOHANNES HEIDENHAIN GmbH		13.11.2012	D 590652-06 - B-01	1 of 1
83301 Traunreut, Germany		Document number		