



Temperatursensor / Temperature sensor

⊗
⊗
(B)

Biegeradius min. / min. bend radius

3mm

Durchmesser / Diameter

2,0mm

Querschnitt / Cross section

0,16mm² / AWG26

Biegeradius min. dauernd

--

Min. bend radius for flexing

(A)

Biegeradius min. einmalig

10mm

Min. bend radius for rigid configuration

Schleppkettenradius min.

--

Min. drag chain radius

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps

For max. cable length (L): See Specifications of the encoder model

886 200 A4

			IDnumber:
			Change No. C010352-06 Phase: Serie
	Original drawing	AGK JAE --> Litzen Netzschlauch (01)	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Scale	Format		Allgemeintoleranzen ISO 2768-mH ±0,2mm: +- 0,2 General tolerances ISO 2768-mH ±0,2mm: +- 0,2
Dimensions in mm	1:1	A4	Anschlussmaße

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

HEIDENHAIN

DR. JOHANNES HEIDENHAIN GmbH
83301 Traunreut, Germany

Document number

D 652661 - 00 - B - 47

1
of

Version | Revision | Sheet

1