



Temperatursensor / Temperature sensor	
Biegeradius min. / min. bend radius	5mm
Durchmesser / Diameter	3mm
Querschnitt / Cross section	0,25mm ²
Biegeradius min. dauernd Min. bend radius for flexing	--
A Biegeradius min. einmalig Min. bend radius for rigid configuration	18mm
Schleppkettenradius min. Min. drag chain radius	--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.01 / D1218918 Bl.02
required mating dimensions see D1140890 Bl.01 / D1218918 Bl.02

Lochkreis-Durchmesser 28mm
bolt-hole circle diameter 28mm

Original drawing		AGK JAE --> Winkeldose M23 (68Sxx)		IDnumber:
Scale	Format	Anschlussmaße		Change No. C056908-18 Phase: Serie
Dimensions in mm	1:1	A3		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
				Allgemeintoleranzen ISO 2768-mH ±6mm: + 0,2 General tolerances ISO 2768-mH ±6mm: + 0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)				
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version	Revision
			Sheet	
			D 652661 - 03 - A - 03	
			Document number	
			1 of 1	