

Biegeradius min. dauernd  
Min. bend radius for flexing

50mm


Biegeradius min. einmalig  
Min. bend radius for rigid configuration

18mm

⊗ Schleppkettenradius min.  
Min. drag chain radius

50mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
For max. cable length (L): See Specifications of the encoder model



886 200 A4

			IDnumber:
			Change No. C014973-05 Phase: Serie
	Original drawing Scale	Format	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Dimensions in mm	1:1	A4	Allgemeintoleranzen ISO 2768-mH ±0,2 General tolerances ISO 2768-mH ±0,2
		AGK FCI --> Kupplung M12 (1SS08)	
		Anschlussmaße	

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )

**HEIDENHAIN**  
DR. JOHANNES HEIDENHAIN GmbH  
83301 Traunreut, Germany

Document number		
D 652661 - 00 - A - 53		
Version	Revision	Sheet
		1 of 1