



Biegeradius min. dauernd
 Min. bend radius for flexing 75mm

 Biegeradius min. einmalig
 Min. bend radius for rigid configuration 20mm

 Schleppkettenradius min.
 Min. drag chain radius 75mm

 max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
 For max. cable length (L): See Specifications of the encoder model

| | | | |
|---|------------------|----------------------------------|---|
| | | | IDnumber: |
| | | | Change No. C047019-05 Phase: Serie |
| | Original drawing | AGK FCI --> Kupplung M23 (03Sxx) | |
| | Scale | Format | Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015 |
| Dimensions in mm | 1:1 | A3 | Allgemeintoleranzen ISO 2768-mH ±0,2mm; + 0,2 General tolerances ISO 2768-mH ±0,2mm; + 0,2 |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | | Document number D 652661 - 00 - A - 56 |
| | | | 1 of 1 Version Revision Sheet |