



M = machine guideway / Maschinenführung
 ML = measuring length / Messlänge
 OL = overall length / Gesamtlänge
 G = gauging points / Messpunkte
 $\leftarrow \rightarrow = 0 \dots ML$
 $\rightarrow +$ = Bewegungsrichtung der Abtasteinheit für steigende Positionswerte
 direction of motion of the scanning unit for ascending position values
 A = cable / Anschlusskabel
 K = customer mounting dimensions / kundenseitige Anschlussmaße

optional / Optionen
 P = M5 air inlet / M5 Luftanschluss
 S1, S2 = switch signals / Schaltsignale
 RI = selectable reference mark / wählbare Referenzmarke
 * = actuator magnet / Schaltmagnet
 ** = sensor position / Sensorposition

Original drawing		MSA770		ID number: -
Scale		MSA770		Change No. C157360-16
Format		Anschlussmaße / Mating Dimensions		Phase: Serie
Dimensions in mm		1:1 A2		Tolerances as per ISO 8015
				General Tolerances ISO 2768:1989-mH ≤ 6:±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of a patent, utility model or design. (ISO 16016)				
Released		Version		Revision
23.11.2023		D 670864-01-B-01		Sheet 1 of 1
www.rsfsf.at		Document number		