



| Toleranztabelle | |
|-----------------|--------|
| L | T |
| <= 250mm | ± 5mm |
| < 1000mm | + 10mm |
| <= 3000mm | + 30mm |
| > 3000mm | + 1% |

Biegeradius min. dauernd
Min. bend radius for flexing

Biegeradius min. einmalig
Min. bend radius for rigid configuration

Schleppkettenradius min.
Min. drag chain radius

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

| | | | |
|--|---------------------------|--------|---|
| | | | IDnumber: |
| | | | Change No. C093830-05 Phase: Serie |
| | Original drawing Scale | Format | AGK JAE --> Kuplung M12 (1SS08) Anschlussmaße |
| Dimensions in mm | 1:1 | A3 | |
| | | | Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015 |
| | | | Allgemeintoleranzen ISO 2768-mH ±0.2mm; + 0.2 General tolerances ISO 2768-mH ±0.2mm; + 0.2 |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | | Version Revision Sheet D 652661 - 00 - A - 59 Document number |

866 200 A3