



EK	Anschluss-Belegung Elektrischer Anschluss
	
	Geometrie Polbild (Steckseite)
JH	Firmenname
..	Ausgangssignal
Sensorb.	Eingangssignal
EnDat22	Datenschnittstelle
..	Teilkreiszusatzspur
12 polig	Kundenseitige Steckerausführung
12	Versorgung 0V (Un)
5	Versorgung 0V (Sensorleitung)
1	Versorgung +V (Up)
11	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
Gehäuse	Außenschirm
6	Serielle Datenübertragung Daten
7	Serielle Datenübertragung Daten invers
9	Serielle Datenübertragung Takt
8	Serielle Datenübertragung Takt invers
10	Serielle Datenübertragung Sensorinterface+
2	Serielle Datenübertragung Sensorinterface-
3	Freie Adern und Pins
4	Freie Adern und Pins

EK	Pin configuration Electrical connection
	
	Geometry of pole pattern (plug side)
JH	company name
..	Output signal
Sensorb.	Input signal
EnDat22	Data interface
..	Additional circular scale track
12-pin	Customer's connection version
12	Supply 0V (Un)
5	Supply 0V (sensor line)
1	Supply +V (Up)
11	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
Housing	External shield
6	Serial data transfer of data
7	Serial data transfer of data, inverted
9	Serial data transfer of clock pulse
8	Serial data transfer of clock pulse, inverted
10	Serial data transfer of sensor interface+
2	Serial data transfer of sensor interface-
3	Free wires and pins
4	Free wires and pins

Connection layout EK 7KS12 .. EnDat22 Sensorb. ..		Pin Layout		Change No. C091467-22	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		D680849	- 00	- A	- 12
		Document No			Page 1/1