



- Temperatursensor / Temperature sensor
- Biegeradius min. / min. bend radius 5mm
- (B) Durchmesser / Diameter 3,0mm
- Querschnitt / Cross section 0,25mm<sup>2</sup>
- Biegeradius min. dauernd / Min. bend radius for flexing --
- (A) Biegeradius min. einmalig / Min. bend radius for rigid configuration 18mm
- Schleppkettenradius min. / Min. drag chain radius --

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
 For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.02 / D1218918 Bl.01  
 required mating dimensions see D1140890 Bl.02 / D1218918 Bl.01

Lochkreis-Durchmesser 28mm  
 bolt-hole circle diameter 28mm

			IDnumber:
			Change No. C129951-21 Phase: Serie
	Original drawing Scale   Format	AGK FCI --> Winkeldose M23-SpeedTEC (2J)	Tolerances as per ISO 8015
Dimensions in mm	1:1   A3	Anschlussmaße	General Tolerances ISO 2768:1989-mH ±0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 20.06.2022	Version   Revision   Sheet D 652661 - 00 - E - 66 1 of 1
		Document number	