



EK	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
..	Ausgangssignal
Sensorb.	Eingangssignal
Fanuc	Datenschnittstelle
..	Teilkreiszusatzspur
12 polig	Kundenseitige Steckerausführung
12	Versorgung 0V (Un)
5	Versorgung 0V (Sensorleitung)
1	Versorgung +V (Up)
11	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
Gehäuse	Außenschirm
6	Serielle Datenübertragung serial Data
7	Serielle Datenübertragung serial Data invers
9	Serielle Datenübertragung Request Frame
8	Serielle Datenübertragung Request Frame invers
10	Serielle Datenübertragung Sensorinterface+
2	Serielle Datenübertragung Sensorinterface-
3	Freie Adern und Pins
4	Freie Adern und Pins

EK	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
..	Output signal
Sensorb.	Input signal
Fanuc	Data interface
..	Additional circular scale track
12-pin	Customer's connection version
12	Supply 0V (Un)
5	Supply 0V (sensor line)
1	Supply +V (Up)
11	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
Housing	External shield
6	Serial data transfer of serial data
7	Serial data transfer of serial data, inverted
9	Serial data transfer of Request Frame
8	Serial data transfer of Request Frame, inverted
10	Serial data transfer of sensor interface+
2	Serial data transfer of sensor interface-
3	Free wires and pins
4	Free wires and pins

Connection layout EK 7KS12 .. Fanuc Sensorb. ..		Pin Layout		Change No. C091467-22	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		D680849	- 00	- A	- 13
		Document No			Page 1/1