



	Temperatursensor / Temperature sensor	
(B)	Biegeradius min. / min. bend radius	10mm
	Durchmesser / Diameter	4,5mm
	Querschnitt / Cross section	0,25mm <sup>2</sup>
	Biegeradius min. dauernd Min. bend radius for flexing	--
(A)	Biegeradius min. einmalig Min. bend radius for rigid configuration	18mm
	Schleppkettenradius min. Min. drag chain radius	--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.01 / D1218918 Bl.02  
required mating dimensions see D1140890 Bl.01 / D1218918 Bl.02

Lochkreis-Durchmesser 28mm  
bolt-hole circle diameter 28mm

		IDnumber:
		Change No. C056908-18 Phase: Serie
	Original drawing Scale   Format	AGK JAE --> Winkeldose M23 (68Sxx)
Dimensions in mm	1:1   A3	Anschlussmaße
		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
		Allgemeintoleranzen ISO 2768-mH ±0,2mm; +0,2 General tolerances ISO 2768-mH ±0,2mm; +0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )		
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version   Revision   Sheet D 652661 - 02 - A - 50 Document number
		1 of 1