



FC	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
..	Ausgangssignal
~2Vss	Eingangssignal
..	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
1+2	Versorgung 0V (Un)
3+4	Versorgung +V (Up)
Gehäuse	Außenschirm
5	Spannungssignal A+
6	Spannungssignal B+
7	Zusätzliche Signale Referenzspannung Vref
8	Zusätzliche Signale Scale ABS (RI)
9	Zusätzliche Signale Alarm
15	Zusätzliche Signale Gehäusepotential 0V
10; 11; 12; 13; 14	Freie Adern und Pins

FC	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
..	Output signal
~2Vpp	Input signal
..	Data interface
..	Additional circular scale track
15-pin	Customer's connection version
1+2	Supply 0V (Un)
3+4	Supply +V (Up)
Housing	External shield
5	Voltage signal A+
6	Voltage signal B+
7	Additional signals reference voltage Vref
8	Additional signals Scale ABS (RI)
9	Additional signals Alarm
15	Additional signals housing potential 0V
10; 11; 12; 13; 14	Free wires and pins

Connection layout FC 59B15 ~2Vpp .. JH	Pin Layout	Change No: C059124-22
--	------------	-----------------------

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

HEIDENHAIN
DR. JOHANNES HEIDENHAIN GmbH

Serie	Version	Revision	Sheet	Page
D683563	- 01	- A	- 01	1/1
Document No				