



EK	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
..	Ausgangssignal
..	Eingangssignal
Pana02	Datenschnittstelle
..	Teilkreiszusatzspur
12 polig	Kundenseitige Steckerausführung
12	Versorgung 0V (Un)
5	Versorgung 0V (Sensorleitung)
1	Versorgung +V (Up)
11	Versorgung +V (Sensorleitung)
Im Messgerät	Versorgung verbunden mit Sensorleitung
Gehäuse	Außenschirm
9	Serielle Datenübertragung REQ/Serial Data +
8	Serielle Datenübertragung REQ/Serial Data -
2;3;4;6;7;10	Freie Adern und Pins

EK	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
..	Output signal
..	Input signal
Pana02	Data interface
..	Additional circular scale track
12-pin	Customer's connection version
12	Supply 0V (Un)
5	Supply 0V (sensor line)
1	Supply +V (Up)
11	Supply +V (sensor line)
In the encoder	Supply connected with sensor line
Housing	External shield
9	Serial data transfer of REQ/Serial Data +
8	Serial data transfer of REQ/Serial Data -
2;3;4;6;7;10	Free wires and pins

Connection layout EK 7KS12 .. Pana02 JH				Pin Layout		Change No. C091467-21	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D680849	- 00	- A	- 11	1/1	
83301 Traunreut, Germany		Document No					