



<b>SB</b>	<b>Anschluss-Belegung</b>	
	<b>Elektrischer Anschluss</b>	
	<b>Geometrie Polbild (Steckseite)</b>	
<b>JH</b>	<b>Firmenname</b>	<b>JH</b>
..	<b>Ausgangssignal</b>	..
..	<b>Eingangssignal</b>	..
<b>EnDat22</b>	<b>Datenschnittstelle</b>	<b>EnDat22</b>
..	<b>Teilkreiszusatzspur</b>	..
9 polig	Kundenseitige Steckerausführung	Ader
4	Versorgung 0V (Un)	weißgrün
8	Versorgung 0V (Sensorleitung)	weiß
3	Versorgung +V (Up)	braungrün
7	Versorgung +V (Sensorleitung)	blau
Im EBB	Versorgung verbunden mit Sensorleitung	Im EBB
Gehäuse	Außenschirm	Schirm
5	Serielle Datenübertragung Daten	grau
6	Serielle Datenübertragung Daten invers	rosa
1	Serielle Datenübertragung Takt	violett
2	Serielle Datenübertragung Takt invers	gelb
9	Freie Adern und Pins	

<b>SB</b>	<b>Pin configuration</b>	
	<b>Electrical connection</b>	
	<b>Geometry of pole pattern (plug side)</b>	
<b>JH</b>	<b>company name</b>	<b>JH</b>
..	<b>Output signal</b>	..
..	<b>Input signal</b>	..
<b>EnDat22</b>	<b>Data interface</b>	<b>EnDat22</b>
..	<b>Additional circular scale track</b>	..
9-pin	Customer's connection version	Wire
4	Supply 0V (Un)	white and green
8	Supply 0V (sensor line)	white
3	Supply +V (Up)	brown and green
7	Supply +V (sensor line)	blue
In EBB	Supply connected with sensor line	In EBB
Housing	External shield	Shield
5	Serial data transfer of data	grey
6	Serial data transfer of data, inverted	pink
1	Serial data transfer of clock pulse	violet
2	Serial data transfer of clock pulse, inverted	yellow
9	Free wires and pins	

Connection layout SB JIS09 .. EnDat22 .. .. JH		Pin Layout		Change No: C001061-10	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Serie	Version	Revision	Sheet
		<b>D745739</b>	<b>- 00</b>	<b>- B</b>	<b>- 15</b>
		Document No			Page 1/1