



- A** = Lagerung Kundenwelle
Bearing for customer shaft
- K** = Kundenseitige Anschlussmaße
Required mating dimensions
- M** = Messpunkt Arbeitstemperatur
Operating temperature measuring point
- H1** = Nullposition ± 15°
Zero position ± 15°
- H2** = Klemmelement SW3 (3x120°), Md= 2,5 +0,5Nm
Locking element SW3 (3x120°), Md= 2,5 +0,5Nm
- H3** = Ausgleich von Montagetoleranzen und thermischer Ausdehnung,
keine dynamische Bewegung
Compensation of mounting tolerances and thermal expansion,
no dynamic motion
- H4** = Berührungsschutz nach EN 60529
Protection according to EN 60529

Ø 50h7	56	58,5	55	47	42D	32C	30A	01 03S17 16S15 35S17
Ø 38h7	56	58,5	55	47	42C			
Ø 25h7	41	43,5	40	32	42B	33C		
Ø 20h7	41	43,5	40	32	42A			
D	L1	L2	L3	L4	WELLA1	FLANA1	KUPPA1	ANELA1

Original drawing			ECN 113		ID number:	
Scale			ECN 113		Change No. C006799-15	
Format			Anschlussmaße / Mounting Dimensions		Phase: Serie	
Dimensions in mm			1:1 A2		Tolerierung nach DIN ISO 8015	
					Allgemeintol. ISO 2768-mH ±6mm:±0,2	
					General tol. ISO 2768-mH ±6mm:±0,2	

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)