



1 213 928 A2

M = machine guideway / Maschinenführung
 ML = measuring length / Messlänge
 ∓ = 0...ML
 * = max. change in operation / max. Änderung bei Betrieb
 C = cable / Anschlusskabel
 (K) = customer mounting dimensions / kundenseitige Anbaumaße
 k = any position of reference mark / beliebige Position der Referenzmarke
 BO = glass ceramic scale without adhesive tape / Glaskeramikmaßstab ohne Klebeband
 BK = glass ceramic scale with adhesive tape / Glaskeramikmaßstab mit Klebeband

Option:
 S1, S2 = switch signals / Schaltsignale
 ** = sensor position / Sensorposition

Dimensions in mm: 1:1 A2
 Original drawing Scale: 1:1 A2
 MS82 BK/BO
 MS82 BK/BO
 Anschlussmaße / Mating Dimensions

ID number: -
 Change No. C157360-28
 Phase: Serie
 Tolerances as per ISO 8015
 General Tolerances ISO 2768:1989-mH ≤ 6±0.2

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)