




ML > 220 mm (LC/LS)
ML > 200 mm (LF)

170 mm <= ML <= 220 mm (LC/LS)
150 mm <= ML <= 200 mm (LF)

70 mm <= ML <= 150 mm (LC/LS)
50 mm <= ML <= 130 mm (LF)

ML 25/50/55 mm (LC/LS)

LS/LC
Messlänge

LF 485/
485C
Messlänge

d

ML <=820 P1...P2 LC/LS
ML <=800 P1...P2 LF
ML > 820 P1...P3 LC/LS
ML > 800 P1...P3 LF

(K) = Kundenseitige Anschlussmaße Required mating dimensions

P = Messpunkte zum Ausrichten Gauging point for alignment
F = Maschinenführung Machine guideway
ML = Messlänge Measuring length

			ID number: 770902-00
			Change No. C183029-05
			Phase: Serie
	Original drawing	Scale	Format
	Dimensions in mm	1:1	A1
Montageschiene mounting spar			Tolerances as per ISO 8015
Anschlussmaße / Mating Dimensions			General Tolerances ISO 2768:1999-mH ± 6mm; ±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18016)			
Released		Version / Revision	Sheet
18.02.2025		D 800615-06 - A-01	1 of 1
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Document number