



	d	R	R
		Feste Verlegung Rigid configuration	Wechselbiegung Frequent flexing
PUR	D 3.7 mm	> 8 mm	>= 40 mm
PUR	D 2.9 mm	> 6 mm	>= 30 mm

- I II III = Montagemöglichkeiten / Mounting options
- F = Maschinenführung / Machine guideway
- * = Anbaufehler plus dyn. Führungsfehler / Mounting failure plus dyn. failures of guideway
- S = Beginn der Messlänge ML / Beginning of measuring length ML
- L = Maßbandlänge / Scale length
- H1 = Optische Mittellinie / Optical centreline
- H2 = Montageabstand Abtastkopf zu Maßband / Mounting gap
- H3 = Bewegungsrichtung der Abtasteinheit für Ausgangssignale gemäß Schnittstellenbeschreibung / Direction of scanning unit motion for output signals in accordance with interface description

ID number: 826203-01		Change No. C160627-05		Tolerances as per ISO 8015	
Phase: Serie		LIC 41x9		General Tolerances ISO 2768-1:2008-mH ±0.2	
Original drawing Scale Format		LIC 41x9		Released	
Dimensions in mm 1:1 A1		Anschlussmaße / Mating Dimensions		Version / Revision / Sheet / Page	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 10216)		DR. JOHANNES HEIDENHAIN GmbH		15.12.2023	
HEIDENHAIN		D 826203-06 - A-01		1 of 1	
83301 Traunreut, Germany		Document number			