




	d	R	R
		Feste Verlegung Rigid configuration	Wechselbiegung Frequent flexing
PUR	D 3.7 mm	> 8 mm	>= 40 mm



- I II III = Montagemöglichkeiten
 F = Maschinenführung
 * = Max. Änderung bei Betrieb
 S = Beginn der Messlänge ML
 L = Maßbandlänge
 H1 = Optische Mittellinie
 H2 = Montageabstand Abtastkopf zu Maßband
 H3 = Bewegungsrichtung der Abtasteinheit für Ausgangssignale gemäß Schnittstellenbeschreibung
- Mounting options**
 Machine guideway
 Max. change during operation
 Beginning of measuring length ML
 Scale length
 Optical centreline
 Mounting gap
 Direction of scanning unit motion for output signals in accordance with interface description

Original drawing		LIC 21x9		ID number: 827563-01
Scale		LIC 21x9		Change No. C160627-05
Format		Anschlussmaße / Mating Dimensions		Serie
Dimensions in mm	1:1 A1			Tolerances as per ISO 8015
				General Tolerances ISO 2768-1/2001-mH ±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 15015)				
Released		Version / Revision / Sheet		Page
15.12.2023		D 827563-06-A-01		1 of 1
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany				