


Gewindebohrung Kundenseitig M3 ∇ 5
Thread hole for customer's scope of supply M3 ∇ 5

	d	R	R
		Feste Verlegung Rigid configuration	Wechselbiegung Frequent flexing
PUR	D 3.7 mm	> 8 mm	>= 40 mm



- I II III = Montagemöglichkeiten
 F = Maschinenführung
 * = Max. Änderung bei Betrieb
 S = Beginn der Messlänge ML
 T = Träger-Länge
 H1 = Optische Mittellinie
 H2 = Montageabstand Abtastkopf zu Maßband
 H3 = Bewegungsrichtung der Abtasteinheit für Ausgangssignale gemäß Schnittstellenbeschreibung
- Mounting options
 Machine guideway
 Max. change during operation
 Beginning of measuring length ML
 Carrier length
 Optical centreline
 Mounting gap
 Direction of scanning unit motion for output signals in accordance with interface description

ID number: 827880-01		Change No. C160627-05	
Phase: Serie		Tolerances as per ISO 8015	
Original drawing Scale: 1:1 Format: A1		General Tolerances ISO 2768:1989-mH ±0.2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 18015)			
Released: 15.12.2023		Version Revision Sheet Page	
DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		D 827880-06-A-01 1 of 1	